


## BroadCat CAT 5E U/UTP

### Unscreened Twisted Pair 125MHz



### Application

Generic cabling systems. White colour sheath without print legend for open installations.

### Standards

EN 50173-1; ISO/IEC 11801; EN 50288-3-1; IEC61156-5; EIA/TIA 568-B.2

### Fire rating

PVC : IEC 60332-1

### Construction

Conductor	Stranded copper wire, tinned 0.50 mm
Insulation	PE, Ø 0,90 mm
Twisting	2 cores to the pair
Cable lay up	4 pairs
Lay up diameter	Ø 4,0 mm
Sheath	Flame retardant PVC

### Mechanical Properties

Bending radius	Installation	8 x D
	Installed	4 x D
Temperature range	During operation	-20°C to + 60°C
	During installation	0°C to + 50°C
Fire load	4 pair PVC	314 MJ/km
Maximum tensile load, installation	During installation	100N
	Installed	-

## BroadCat CAT 5E U/UTP

### Electrical Properties

at 20°C

DC loop resistance		≤ 170 Ω/km
Resistance unbalance		≤ 2%
Insulation resistance	(500 V)	≥ 5000 MΩxkm
Capacitance	at 800 Hz	Nom. 50 nF/km
Capacitance unbalance	(pair to ground)	≤ 300 pF/km
Mean Characteristic impedance	@ 100 MHz)	100 ± 5 Ω
Nominal velocity of propagation		0,68 c
Propagation delay		≤ 500 ns/100 m
Delay skew		≤ 20 ns/100 m

### Nominal Transmission characteristics

at 20°C

F (MHZ)	Attenuation (dB/100m)	NEXT (dB)	ACR (dB/100m)	Returnloss (dB)	PS- NEXT (dB)	PS-ACR (dB/100m)	ELFEXT (dB/100m)	PS-ELFEXT (dB/100m)
1	1,8	77	75	-	74	72	75	72
4	3,6	70	66	27	67	63	62	59
10	6,0	65	59	30	62	56	56	53
16	7,6	64	56	30	61	53	52	49
20	8,6	62	53	30	59	50	50	47
31.25	11,0	59	48	30	56	45	47	44
62.50	16,0	55	39	30	52	36	43	40
100	20,7	48	27	25	45	24	42	39
125	23,8	48	24	25	45	21	41	38

### Technical Data

Part number	Description	Colour	Outer diameter (D) mm	Weight kg/km
1000855	BroadCat U/UTP PVC 4x2x0.5mm Cat.5e	White, RAL9001	5,2	31

[PRODUCT CODE TABLE]

© PRYSMIAN GROUP 2006, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.